

Cadco, Ltd.

Glass Ceramic Range


Model PHR-1C

How to Use Two-Zone Dial Function



120 volts - 1500 watts- 12.5 amps (8.25" heating zone)
600 watts (5.5" heating zone)

The Glass Ceramic Cooking Surface has a **power-saving two-circle heating zone**, so you can match heating zone diameter to your pot/pan diameter for **maximum energy efficiency!**



- For activating the **large heating zone** (8.25" diameter), turn the Temperature Control Knob **clockwise up to the symbol ©** and then **counterclockwise** back to the desired setting level.
- For changing back to the **small heating zone** (5.5" diameter), turn the temperature Control Knob **counterclockwise** back to **OFF (O)** and then **clockwise** back to the required level 1-12.
- Use the settings as follows:
 - 1-5 - for warming up and keeping warm
 - 4-9 - for moderate temperature cooking
 - 8-12 - for high temperature cooking

Cadco, Ltd.

145 Colebrook River Road, Winsted, CT 06098
(860) 738-2500 • Fax (860) 738-9772

Website: www.cadco-ltd.com.com • E-mail: info@cadco-ltd.com
